



# Guangzhou Huaxi C&T Co.,Ltd.

Add: Room 1502 Hongmian Business Center, No.10 Hualei Road, Liwan District, Guangzhou, Guangdong Province, China

E-mail: [info@choicybeauty.com](mailto:info@choicybeauty.com) Tel:+86-20-38263199 Website: [www.choicybeauty.com](http://www.choicybeauty.com)

## Choicy Beauty Equipment Series

### -- RF Fractional CO2 Vaginal Tightening Laser



**Model: CB-811A**

#### Product Description



## System Characteristics


1. Tightens the vagina and rejuvenates natural flexibility
2. Vaginal remodeling pain free procedure with long-lasting result
3. Greater sexual pleasure and desire.
4. Increase quantity and quality of orgasms achieved during intimacy.
5. Almost non-painful, no need for anesthetics during treatment
6. Improves vaginal dryness and stress urinary incontinence
7. Very short treatment time, just about 15-20min at clinic

## Treatment Range



1. Tighten vagina
2. Clean the vagina
3. Moist vagina
4. Improve skin texture & skin tone
5. Skin resurfacing
6. Collagen contraction and remodeling
7. Pore reduction
8. Pigmentation & age spots removal
9. Photo aged skin and fine lines treatment
10. Scars removal – chicken pox, post acne, post traumatic scars

## Before and After Treatment

### Vaginal Canal Tighten



### Vaginal Tighten





# Guangzhou Huaxi C&T Co.,Ltd.

Add: Room 1502 Hongmian Business Center, No.10 Hualei Road, Liwan District, Guangzhou, Guangdong Province, China

E-mail: [info@choicybeauty.com](mailto:info@choicybeauty.com) Tel:+86-20-38263199 Website: [www.choicybeauty.com](http://www.choicybeauty.com)

## Technical Specifications

Laser type	RF laser tube imported from USA
Laser mode	Super pulse RF laser
Laser spot diameter	D=0.12mm
Single pulse maximum pulse width	500ms
Laser wavelength	10.6 $\mu$ m
Laser output power	1-30w (adjustable)
Spots space	0.2mm-2mm
Working mode	Continuous pulse, Single pulse, Repeat pulse, Super pulse and Magical pulse
Screen	10.4 inch color touch screen
Scan range	20mm*20mm
Input voltage	AC110V/15A/60Hz, AC220V/8A/50Hz
Net weight	55kg

### NOTE:

The detailed instruction will be sent with the equipment.