



## Guangzhou Huaxi C&T Co.,Ltd.

Add: Room 1203, No.66 Huadi South Ave, Liwan District, Guangzhou, Guangdong Province, China

E-mail: [info@choicybeauty.com](mailto:info@choicybeauty.com) Tel:+86-20-38263199 Website: [www.choicybeauty.com](http://www.choicybeauty.com)

### Choicy Beauty Equipment Series -- Phototherapy System



**Model: CB-901C**

#### Product Description





## **Guangzhou Huaxi C&T Co.,Ltd.**

Add: Room 1203, No.66 Huadi South Ave, Liwan District, Guangzhou, Guangdong Province, China

E-mail: [info@choicybeauty.com](mailto:info@choicybeauty.com) Tel:+86-20-38263199 Website: [www.choicybeauty.com](http://www.choicybeauty.com)

### **System Characteristics**

1. LED SYSTEM is a phototherapy machine which professional focuses on increase skin tissue synthesis of collagen and elastin fibres, to produce healthier, faster healing, younger looking and glowing skin.
2. LED technology that generates photons at different frequencies to penetrate into deeper layers of tissue. Different wavelengths (colors blue, infrared, red) of light will have different effects on the skin.
3. LED SYSTEM with Multi functions which is recommended for improving oily skin, removing marks and excess pigmentation, diminishing wrinkles, skin flaccidity, expression lines and orange-peel skin, for firming skin, treating localised adiposity and for whitening teeth.

### **Treatment Range**

1. Remove wrinkles, and pigments on facial skin
2. Skin Rejuvenation and anti-aging
3. Recovery of injured skin:
4. Smooth Lymph and Eliminate Edema.
5. Improve oily skin, to reduce the chances of getting acne.
6. Pain Relief

Add: Room 1203, No.66 Huadi South Ave, Liwan District, Guangzhou, Guangdong Province,  
China

E-mail: info@choicybeauty.com Tel:+86-20-38263199 Website: www.choicybeauty.com

## Before and After Treatment



## Technical Specifications

|                         |   |
|-------------------------|---|
| Model                   | CB-901C                                 |
| LED Dominant Wavelength | RED: 625nm<br>NIR: 810nm<br>BLUE: 470nm |
| Maximum Output          | RED: 200W<br>NIR: 200W<br>BLUE: 200W    |
| Cooling Method          | Air Cooling                             |
| Screen                  | 7 Inch LCD Color Touch Screen           |
| Input Power             | 750W                                    |
| Power Supply            | AC110V/8A/60Hz AC220V/4A/50Hz           |
| Weight                  | 35Kg                                    |

## NOTE:

The detailed instruction will be sent with the equipment.