


ACTMIX ZDMC-70GN F140

Accelerator ZDMC (PZ)

ACTIVE MATERIAL		PROPERTIES:	DOSAGE:
	Zinc dimethyl dithiocarbamate	ZDMC is an ultrafast accelerator of natural and synthetic rubber such as EPDM, SBR, NBR. Thiurams and thiazoles accelerator can delay the start of vulcanization and improve processing safety. Compared to ZDBC,ZDEC and ZEPC, ZDMC has a longer scorching time and shorter curing time, alkaline accelerator can activate it .A little ZDMC is also a assistant accelerator of thiols or thiurams accelerator. Its vulcanizate has excellent tensile strength and resilience.Heat resistance in NR and IR can be improved by using together with antioxidant.	For NR: 0.6-1.0phr; As a secondary accelerator: 0.1-0.2phr For SBR/NBR: 0.6-1.2phr. As a secondary accelerator: 0.1-0.2phr For EPDM: 1.5-2.5phr.
	C ₆ H ₁₂ N ₂ S ₄ Zn		TYPICAL VALUES:
	M.W.: 305.83 CAS: 137-30-4 EINECS: 205-288-3		Initial melting point: Min 242°C Purity: Min 97% Zinc content: 20.5-22.0% Heating loss content: Max 0.5% 63µm sieve residue: Max 0.5%

MASTERBATCH	PRODUCT	Active Content (%)	Appearance	Filtration (µm)	Binder	Sulfur Content (%)	Density (g/cm ³)
	Actmix® ZDMC-70GN F140	69.5	White Granules	140	NBR	31.8	1.46
	* Binder type can be customized. Except NBR, others binders, such as EPDM/EVM, SBR, AR, ECO also can be available for.						
	SAFETY&TOXICITY: Please refer to related SDS.						
PACKAGING&STORAGE: Net weight 25kg/PE bags lined carton; Net weight 600 kg/pallet. Shelf-life: 1 year in its original packaging Stored in a dry and cool place.							

Compared to traditional ZDMC powder, Actmix®ZDMC-70GN F140 allows:

Dust free products with a complete filtration up to 100µm, no skin sensitization, health guard of operators.

Effective guarantee of activity of ZDMC due to pre-dispersed masterbatch.

Tack free products at room temperature, convenience and accuracy on ingredients.

Lower Mooney viscosity at lower temperature (50°C), higher quality of dispersion.

Impurity free, blocked filter free of extrusive products, scrap rate reduction and higher productivity thanks to filtration.

Wider compatibility with other elastomers.

G: granule, P: plate, E: EPDM binder, N: NBR binder, S: SBR binder, A: ACM binder, EO: ECO binder, F140: filtration and micron number of filter

The information contained in this leaflet is based on tests carried out by our laboratories and data selected from references. Therefore it is not valid legally and does not signify any guarantee to customers of successful applications of the product according to their own formulas. However, our company will offer professional services in technology at utmost to facilitate customers to achieve expected purpose of product applications.